



SEAWARD
ELECTRICAL SAFETY TESTING
& MEASURING.

All of my Insulation Resistance test values are around “0.05M Ω or less”?

This is normally an indication that Earth and Neutral are connected together in the installation. Readings should be greater than 1M Ω for an Earthed system, or 2M Ω for Class 2 or “floating” systems. Ideally this reading should be as high as possible. PV150 can read up to 19.99M Ω , and the PV200/210 up to 199.99M Ω . A good result would be “>19.99M Ω ” on the PV150, and “>199.99M Ω ” on the PV200/210.

If you require more help, please contact us at
<https://www.seaward.com/login/enquire/>.